

AUTO LINK PAL FUSES - 2938

RoHS



Description

PAL fuses are commonly found on many Japanese and domestic built vehicles.

Specifications

Voltage Rating: 32 VDC
 Current Cycling: 24°C
 The fuses satisfy the performance requirements after 50% of the rated current is applied for 10,000 cycles. Each cycle consists of an interrupted current with the pattern of 5 minutes ON and 10 minutes OFF.
 Operating Temperature Range: -40°C to +125°C

Complies with JASO 0612

Ordering Information

Part Number	Package Size
02938xxx.H	100
02938xxx.U	500
02938xxx.MXJ	1000

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
110	14,400 s
200	5 s / 100 s
350	0.2s / 7 s
600	0.040 s / 1 s

Ratings

Part Number	Current Rating (A)	Body Color
0293820_	20	LIGHT BLUE
0293830_	30	PINK
0293840_	40	GREEN
0293850_	50	RED
0293860_	60	YELLOW
0293870_	70	BROWN
0293880_	80	BLACK

Dimensions

Dimensions in mm

