


281/282 Series Panel Mount Holders for MICRO™/TR3 Fuses


281 Series Panel Mount



Front of Panel Mounting with Push-On / Rear Retaining Nut

Dimensions units in inch (mm)

0281 0001 Front of Panel Mounting with Push-On / Rear Retaining Nut



282 Series Panel Mount - Sealed/Moisture Resist Knob

Note: These products are shipped unassembled and without fuse device




Rear of Panel Mounting with Threaded Knurled / Front Retaining Nut


Front of Panel Mounting with Threaded Hex / Rear Retaining Nut

Dimensions units in inch (mm)

0282 0002 and 0282 0008 Rear of Panel Mounting with Threaded Knurled / Front Retaining Nut



0282 0001 and 0282 0007 Front of Panel Mounting with Threaded Hex / Rear Retaining Nut



Product Characteristics

| Compatible Fuses | MICRO™/TR3 |
|---------------------------|--|
| Description | Panel mount holder designed for Littelfuse MICRO™/TR3 type and other fuse series with .025" diameter leads rated to 5 amps |
| Electrical Specs | Rated at 5 amperes for any voltage up to 125 |
| Mounting Specs | Maximum panel thickness is .09" |
| Ambient Temp. | -40°C to +125°C |
| Retaining Hardware | "Push-On" retaining nut |
| Molded Material | Black Thermoset |
| Terminal Material | Beryllium copper with silver plating |

Product Characteristics

| Compatible Fuses | MICRO™/TR3 |
|---------------------------------------|--|
| Description | RF-shielded and drip-proof screw-on knob design enables use of Littelfuse MICRO™/TR3 fuses when presence of moisture exists at front of panels |
| Electrical Specs | Rated at 5 amperes for any voltage up to 125 |
| Mounting Specs | Front panel mount, maximum panel thickness: .093" Rear panel mount, maximum panel thickness: .125" |
| Ambient Temp. | -40°C to +125°C |
| Mounting Gasket Options | Neoprene (282001, 282002) or Conductive Silicone (282007, 282008) |
| Retaining Hardware Options | Threaded Hex Nut (282002, 282008) or Threaded Knurled Nut (282001, 282007) |
| Molded Material | Black thermoset |
| Housing, Knob and Nut Material | Aluminum, untreated |
| Terminal Material | Beryllium copper with silver plating |
| Knob Seal | Buna "N" O-ring inside the knob |

Note: Refer to [Fuseology](#) for information on proper fuseholder re-rating.

Additional Information



Datasheet
281 Series



Resources
281 Series



Samples
281 Series



Datasheet
282 Series



Resources
282 Series



Samples
282 Series

Ordering Information

| Ordering Number | Packing |
|-----------------|-------------------|
| 02810001H | Bulk (100 Pieces) |

| Ordering Number | | Gasket Type | Packing |
|---|--------------------------------------|---------------------|-------------------|
| Rear Mounting (Threaded Knurled Nut) | Front Mounting (Threaded Hex Nut) | | |
| 02820002Z | 02820001Z | Neoprene | Bulk (100 Pieces) |
| 02820008Z | 02820007Z | Conductive Silicone | Bulk (100 Pieces) |

Note: These products are shipped unassembled and without fuse device