

UL Product iQ™



NRNT8.E47258 - SWITCHES, INDUSTRIAL CONTROL CERTIFIED FOR CANADA - COMPONENT

Switches, Industrial Control Certified for Canada - Component

See General Information for Switches, Industrial Control Certified for Canada - Component

LITTELFUSE INC

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

E47258

Investigated to CAN/CSA C22.2. No. 14-10

Industrial control switches Model(s) HE3621A6012, HE721A0520, HE721A0540, HE721A1220, HE721A1230, HE721A1240, HE721A2405, HE721A2430, HE721A6022, HE721B0500, HE721B1200, HE721B1220, HE721B2410, HE721B2430, HE721C0520, HE721C0540, HE721C1210, HE721C2440, HE721C2450, HE721C6791, HE721E2410, HE722A0510, HE722A1200

Magnetic reed relays, "HE Series" Model(s) HE3621A+, HE3621B+, HE3651A+, HE3651B+, HE3671A+, HE3671B+

Magnetic reed relays Model(s) HE321A0400, HE321A0440, HE321A0500, HE321A0540, HE321A1200, HE321A1240, HE321A2400, HE321A2440, HE321A5014, HE321B0400, HE321B0440, HE321B0500, HE321B0540, HE321B1200, HE321B1240, HE321B2400, HE321B2440, HE331A0500, HE331A0540, HE331A1200, HE331A1240, HE331A2400, HE331A2440, HE3321A, HE3321A0400, HE3321A0400(*), HE3321A0440, HE3321A0440(*), HE3321A0470(*), HE3321A0500(*), HE3321A0540(*), HE3321A0570(*), HE3321A1200, HE3321A1200(*), HE3321A1240(*), HE3321A1270(*), HE3321A2400, HE3321A2400(*), HE3321A2440, HE3321A2440(*), HE3321A2470(*), HE3321A6376, HE3321A6645, HE3321B0400(*), HE3321B0440(*), HE3321B0470(*), HE3321B0500(*), HE3321B0540(*), HE3321B0570(*), HE3321B1200(*), HE3321B1240(*), HE3321B1270(*), HE3321B2400(*), HE3321B2440(*), HE3321B2470(*), HE3321C, HE3321C0400, HE3321C0400(*), HE3321C0440(*), HE3321C0470(*), HE3321C0500, HE3321C0500(*), HE3321C0540(*), HE3321C0570(*), HE3321C1200, HE3321C1200(*), HE3321C1240(*), HE3321C1270(*), HE3321C2400, HE3321C2400(*), HE3321C2440(*), HE3321C2470(*), HE3321C6675, HE3321E, HE3321E0400(*), HE3321E0440(*), HE3321E0470(*), HE3321E0500(*), HE3321E0540(*), HE3321E0570(*), HE3321E1200, HE3321E1200(*), HE3321E1240(*), HE3321E1270(*), HE3321E2400(*), HE3321E2440(*), HE3321E2470(*), HE3321E5940, HE3321E5941, HE3321E5942, HE3331A0400(*), HE3331A0440(*), HE3331A0470(*), HE3331A0500(*), HE3331A0540(*), HE3331A0570(*), HE3331A1200(*), HE3331A1240(*), HE3331A1270(*), HE3331A2400(*), HE3331A2440(*), HE3331A2470(*), HE3331B0400(*), HE3331B0440(*), HE3331B0470(*), HE3331B0500(*), HE3331B0540(*), HE3331B0570(*), HE3331B1200(*), HE3331B1240(*), HE3331B1270(*), HE3331B2400(*), HE3331B2440(*), HE3331B2470(*), HE3331C0400(*), HE3331C0440(*), HE3331C0470(*), HE3331C0500(*), HE3331C0540(*), HE3331C0570(*), HE3331C1200(*), HE3331C1240(*), HE3331C1270(*), HE3331C2400(*), HE3331C2440(*), HE3331C2470(*), HE3331E0400(*), HE3331E0440(*), HE3331E0470(*), HE3331E0500(*), HE3331E0540(*), HE3331E0570(*), HE3331E1200(*), HE3331E1240(*), HE3331E1270(*), HE3331E2400(*), HE3331E2440(*), HE3331E2470(*), HE3351A0400(*), HE3351A0440(*), HE3351A0470(*), HE3351A0500, HE3351A0500(*), HE3351A0540(*), HE3351A0570(*), HE3351A1200, HE3351A1200(*), HE3351A1240(*), HE3351A1270(*), HE3351A2400, HE3351A2400(*), HE3351A2440(*), HE3351A2470(*), HE3351A6886, HE3351AH, HE3351B0400(*), HE3351B0440(*), HE3351B0470(*), HE3351B0500(*), HE3351B0540(*), HE3351B0570(*), HE3351B1200(*), HE3351B1240(*), HE3351B1270(*), HE3351B2400(*), HE3351B2440(*), HE3351B2470(*), HE3351C0400(*), HE3351C0440(*), HE3351C0470(*), HE3351C0500(*), HE3351C0540(*), HE3351C0570(*), HE3351C1200(*), HE3351C1240(*), HE3351C1270(*), HE3351C2400(*), HE3351C2440(*), HE3351C2470(*), HE3351E0400(*), HE3351E0440(*), HE3351E0470(*), HE3351E0500(*), HE3351E0540(*), HE3351E0570(*), HE3351E1200(*), HE3351E1240(*), HE3351E1270(*), HE3351E2400(*), HE3351E2440(*), HE3351E2470(*), HE3361A0400(*), HE3361A0440(*), HE3361A0470(*), HE3361A0500(*), HE3361A0540, HE3361A0540(*), HE3361A0570(*), HE3361A1200(*), HE3361A1240(*), HE3361A1270(*), HE3361A2400(*),

HE3361A2440(*), HE3361A2470(*), HE3361B0400(*), HE3361B0440(*), HE3361B0470(*), HE3361B0500(*), HE3361B0540(*), HE3361B0570(*), HE3361B1200(*), HE3361B1240(*), HE3361B1270(*), HE3361B2400(*), HE3361B2440(*), HE3361B2470(*), HE3361C0400(*), HE3361C0440(*), HE3361C0470(*), HE3361C0500(*), HE3361C0540(*), HE3361C0570(*), HE3361C1200(*), HE3361C1240(*), HE3361C1270(*), HE3361C2400(*), HE3361C2440(*), HE3361C2470(*), HE3361E0400(*), HE3361E0440(*), HE3361E0470(*), HE3361E0500(*), HE3361E0540(*), HE3361E0570(*), HE3361E1200(*), HE3361E1240(*), HE3361E1270(*), HE3361E2400(*), HE3361E2440(*), HE3361E2470(*), HE341A0500, HE341A0540, HE341A1200, HE341A1240, HE341A2400, HE341A2440, HE351A0500, HE351A0540, HE351A1200, HE351A1240, HE351A2400, HE351A2440, HE361A0500, HE361A0540, HE361A1200, HE361A1240, HE361A2400, HE361A2440, HE361A5010, HE3621A, HE3621A0500, HE3621A0510, HE3621A0540, HE3621A0550, HE3621A1200, HE3621A1210, HE3621A1250, HE3621A2400, HE3621A2410, HE3621A6684, HE3621A6685, HE3621A6786, HE3621A6847, HE3621A6849, HE3621A6854, HE3651A, HE3671A, HE3671A0500, HE3671A0510, HE3671A1200, HE421A5069, HE421A5181, HE421A5182, HE421A5183, HE421A5258, HE421A5259, HE421A5260, HE421A5318, HE421A5328, HE421A5376, HE421A5390, HE421A5391, HE421A6221, HE422B5449, HE451A5393, HE461A0504, HE461A1204, HE461A2404, HE561-A5050, HE561-B5051, HE721A0500, HE721A0510, HE721A0530, HE721A1200, HE721A1201, HE721A1210, HE721A2400, HE721A2406, HE721A2410, HE721A2415, HE721B0510, HE721B0530, HE721B0540, HE721B0550, HE721B1210, HE721C0500, HE721C0510, HE721C0530, HE721C1200, HE721C1230, HE721C1250, HE721C2400, HE721C2410, HE721C2430, HE721E0510, HE721E1200, HE721E1230, HE721E2400, HE721R0500, HE721R0510, HE721R1210, HE721R2410, HE722A0500, HE722A0530, HE722A0600, HE722A0610, HE722A1210, HE722A1250, HE722A2400, HE722A2410, HE751A0500, HE751A0510, HE751A1200, HE751A1210, HE751A2400, HE751A2410

Open type reed relays for use in electronic data processing equipment, office appliances and business equipment Model(s)
HE722A+, HE751A+

Reed relays, for use in electronic data processing equipment, office appliances and business equipment, open type Model(s)
HE721A, HE721B, HE721C, HE721E, HE721R

Reed switches Model(s) BASE-14, DRR-129, DRS-50, DRS-DTH, FLEX-14

Reed Switches Model(s) HA15-2

Reed switches Model(s) MACD-14, MARR-2, MARR-5, MASM-14, MATE-12, MDCG-4, MDRR-6, MDRR-DT, MDSM-10B, MDSM-4B, MDSM-4R, MDSM-7B, MDSM-7R, MDSM-DTB, MDSM-DTR, MDSR-10, MDSR-10R, MDSR-4, MDSR-7, MISM-3V1x, where x can be B or R., MITI-3V1, MITI-7x and MISM-7x, where x can be B or R., MLRR-2, MLRR-3, MLRR-4, MLSM-3B, MLSM-3R, MLSM-4B, MLSR-4R, MRPR-1, MRPR-2, MRPR-20, MRPR-3, MRPR-8, MVSR-20

(*) - Last four digits may be replaced by 5000 to 9999 incl.

+ - Followed by 0000 through 9999.

Marking: Company name or trademark  ,  , model designation and the Recognized Component Mark for Canada,  on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2018-03-20

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"