



Advance Data

High Power Sonic FRD

Type E1780TG65E

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V _{RRM}	Repetitive peak reverse voltage, (note 1)	6500	V
V _{RSM}	Non-repetitive peak reverse voltage, (note 1)	6600	V
V _{R(d.c.)}	Maximum reverse d.c. voltage (note 1)	3600	V

	OTHER RATINGS (note 6)	MAXIMUM LIMITS	UNITS
I _{F(AV)M}	Mean forward current, T _{sink} =55°C, (note 2)	1780	A
I _{F(AV)M}	Mean forward current. T _{sink} =100°C, (note 2)	1109	A
I _{F(AV)M}	Mean forward current. T _{sink} =100°C, (note 3)	598	A
I _{F(AV)M}	Mean forward current. T _{sink} =100°C, (note 4)	780	A
I _{F(RMS)}	Nominal RMS forward current, T _{sink} =25°C, (note 2)	3354	A
I _{F(d.c.)}	D.C. forward current, T _{sink} =25°C, (note 5)	3023	A
I _{FSM}	Peak non-repetitive surge t _p =10ms, V _{RM} =60%V _{RRM} , (note 6)	25.6	kA
I _{FSM2}	Peak non-repetitive surge t _p =10ms, V _{RM} ≤10V, (note 6)	28.2	kA
I ² t	I ² t capacity for fusing t _p =10ms, V _{RM} =60%V _{RRM} , (note 6)	3.29×10 ⁶	A ² s
I ² t	I ² t capacity for fusing t _p =10ms, V _{RM} ≤10V, (note 6)	3.98×10 ⁶	A ² s
P _{rr}	Maximum non-repetitive peak reverse recovery power, (note 8)	7	MW
T _{j op}	Operating temperature range	-40 to +140	°C
T _{stg}	Storage temperature range	-40 to +150	°C

Notes:-

- 1) De-rating factor of 0.13% per °C is applicable for T_j below 25°C.
- 2) Double side cooled, single phase; 50Hz, 180° half-sinewave.
- 3) Anode side cooled, single phase; 50Hz, 180° half-sinewave.
- 4) Cathode side cooled, single phase; 50Hz, 180° half-sinewave.
- 5) Double side cooled.
- 6) Half-sinewave, 140°C T_j initial.
- 7) Current (I_F) ratings have been calculated using V_{T0} and r_T (see page 2)
- 8) T_j=T_{jop}, I_F=1375A, di/dt=3500A/μs V_r=3600V and L_s=200nH. Test circuit and sample waveform are shown in diagram 1. IGBT type T1375DF65E used as switch.

Characteristics

	PARAMETER	MIN.	TYP.	MAX.	TEST CONDITIONS (Note 1)	UNITS
V_{FM}	Maximum peak forward voltage	-	3.2	3.37	$I_{FM}=1375A$	V
		-	3.6	3.83	$I_{FM}=1780A$	
V_{T0}	Threshold voltage	-	-	2.021	Current range 1375A – 4125A (Note 2)	V
r_T	Slope resistance	-	-	0.983		mΩ
V_{T0}	Threshold voltage	-	-	2.2	Current range 1780A – 5340A (Note 2)	V
r_T	Slope resistance	-	-	0.917		mΩ
V_{FRM}	Maximum forward recovery voltage	-	-	340	$di/dt = 3000A/\mu s, T_J=25^\circ C$	V
		-	-	600	$di/dt = 3000A/\mu s$	
I_{RRM}	Peak reverse current	-	-	1	Rated V_{RRM} , $T_J=25^\circ C$	mA
		-	-	100	Rated V_{RRM}	
Q_{rr}	Recovered charge	-	3500	4200	$I_{FM}=1375A, t_p=1ms, di/dt=3500A/\mu s, V_r=3600V, 50\% \text{ Chord. IGBT type T1375DF65E used as switch}$	μC
Q_{ra}	Recovered charge, 50% Chord	-	970	-		μC
I_{rm}	Reverse recovery current	-	1590	1750		A
t_{rr}	Reverse recovery time, 50% Chord	-	1.22	-		μs
E_{rr}	Reverse recovery energy	-	10	11.5		J
R_{thJK}	Thermal resistance, junction to heatsink	-	-	0.0077	Double side cooled	K/kW
		-	-	0.0129	Cathode side cooled	K/kW
		-	-	0.0188	Anode side cooled	K/kW
F	Mounting force	50	-	60	Note 3)	kN
W_t	Weight	-	1.15	-		kg

Notes:-

- 1) Unless otherwise indicated $T_J=140^\circ C$.
- 2) V_{T0} and r_T were used to calculate the current ratings on page 1.
- 3) For clamp forces outside these limits, please consult factory.

Additional information on Ratings and Characteristics

1.0 De-rating Factor

A blocking voltage de-rating factor of 0.13% per °C is applicable to this device for T_j below 25°C.

2.0 ABCD Constants


These constants (applicable only over current range of V_F characteristic in Figure 1) are the coefficients of the expression for the forward characteristic given below:

$$V_F = A + B \cdot \ln(I_F) + C \cdot I_F + D \cdot \sqrt{I_F}$$


where I_F = instantaneous forward current.

3.0 Reverse recovery ratings

Diagram 1 – Reverse Recovery test circuit and sample waveform



(i) Q_{ra} is based on 50% I_{rm} chord as shown in Figure below.



(ii) Q_{rr} is based on a 40μs integration time.

i.e.

$$Q_{rr} = \int_0^{40\mu s} i_{rr} \cdot dt$$

$$(iii) \quad K \text{ Factor} = \frac{t_1}{t_2}$$

4.0 Reverse Recovery Loss

The following procedure is recommended for use where it is necessary to include reverse recovery loss.

From waveforms of recovery current obtained from a high frequency shunt (see Note 1) and reverse voltage present during recovery, an instantaneous reverse recovery loss waveform must be constructed. Let the area under this waveform be E joules per pulse. A new sink temperature can then be evaluated from:

$$T_{SINK} = T_{J(MAX)} - E \cdot [k + f \cdot R_{th(J-Hs)}]$$

Where k = 0.2314 (°C/W)/s

E = Area under reverse loss waveform per pulse in joules (W.s.)

f = Rated frequency in Hz at the original sink temperature.

R_{th(J-Hs)} = d.c. thermal resistance (°C/W)

The total dissipation is now given by:

$$W_{(tot)} = W_{(original)} + E \cdot f$$

NOTE 1 - Reverse Recovery Loss by Measurement

This device has a low reverse recovered charge and peak reverse recovery current. When measuring the charge, care must be taken to ensure that:

(a) AC coupled devices such as current transformers are not affected by prior passage of high amplitude forward current.

(b) A suitable, polarised, clipping circuit must be connected to the input of the measuring oscilloscope to avoid overloading the internal amplifiers by the relatively high amplitude forward current signal.

(c) Measurement of reverse recovery waveform should be carried out with an appropriate critically damped snubber, connected across diode anode to cathode. The formula used for the calculation of this snubber is shown below:

$$R^2 = 4 \cdot \frac{V_r}{C_s \cdot di/dt}$$

Where: V_r = Commutating source voltage

C_s = Snubber capacitance

R = Snubber resistance

5.0 Computer Modelling Parameters

5.1 Device Dissipation Calculations

$$I_{AV} = \frac{-V_{T0} + \sqrt{V_{T0}^2 + 4 \cdot ff^2 \cdot r_T \cdot W_{AV}}}{2 \cdot ff^2 \cdot r_T}$$

Where $V_{T0} = 2.2V$, $r_T = 0.917m\Omega$

ff = form factor (normally unity for fast diode applications)

$$W_{AV} = \frac{\Delta T}{R_{th}}$$

$$\Delta T = T_{j(MAX)} - T_K$$

5.2 Calculation of V_F using ABCD Coefficients

The forward characteristic I_F Vs V_F , on page 6 is represented in two ways;

- (i) the well established V_{T0} and r_T tangent used for rating purposes and
- (ii) a set of constants A, B, C, and D forming the coefficients of the representative equation for V_F in terms of I_F given below:

$$V_F = A + B \cdot \ln(I_F) + C \cdot I_F + D \cdot \sqrt{I_F}$$

The constants, derived by curve fitting software, are given in this report for both hot and cold characteristics. The resulting values for V_F agree with the true device characteristic over a current range, which is limited to that plotted.

	25°C Coefficients	140°C Coefficients
A	0.5555358	0.4100598
B	0.1386516	0.06491253
C	3.450368×10^{-4}	4.624684×10^{-4}
D	0.02959373	0.05008258

Curves

Figure 1 – Forward characteristics of limit device




Figure 2 – Maximum forward recovery voltage




Figure 3 – Maximum recovered charge, Q_{rr}




Figure 4 – Maximum recovery charge, Q_{ra} (50% chord)




Figure 5 - Maximum reverse current, I_{rm}




Figure 6 - Maximum recovery time, t_{rr} (50% chord)




Figure 7 - Reverse recovery energy per pulse




Figure 8 - Safe operating area




Figure 9 – Transient thermal impedance






Figure 10 – Maximum surge and I^2t ratings



Outline Drawing & Ordering Information



ORDERING INFORMATION

(Please quote 10 digit code as below)

E1780	TG	65	E
Fixed Type Code	Fixed Outline code	Fixed voltage code $V_{RRM}/100$ 65	Fixed code, product series

 Order code: E1780TG65E – 6500V V_{RRM} , 30mm clamp height capsule.

IXYS Long Beach Inc
 2500 Mira Mar Avenue
 Long Beach CA 90815 USA
 Tel: +1 (562) 296 6584
 Fax: +1 (562) 296 6585
 Email: service@ixyslongbeach.com



IXYS
 A Littelfuse Technology

IXYS UK Westcode Ltd
 Langley Park Way, Langley Park,
 Chippenham, Wiltshire, SN15 1GE.
 Tel: +44 (0)1249 455500
 Fax: +44 (0)1249 659448
 E-mail: sales@ixysuk.com

www.littelfuse.com

<https://www.littelfuse.com/products/power-semiconductors/high-power.aspx>

The information contained herein is confidential and is protected by Copyright. The information may not be used or disclosed except with the written permission of and in the manner permitted by the proprietors IXYS UK Westcode Ltd.

© IXYS UK Westcode Ltd.

In the interest of product improvement, IXYS UK Westcode reserves the right to change specifications at any time without prior notice.

Devices with a suffix code (2-letter, 3-letter or letter/digit/letter combination) added to their generic code are not necessarily subject to the conditions and limits contained in this report.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.